

Tpcm[™] 780SP Series

Screen Printable Phase Change Material Preliminary



HIGH PERFORMANCE SCREEN PRINTABLE PHASE CHANGE MATERIAL

Tpcm[™] 780SP is an exceptionally high-performance, screen printable or stencilable thermal interface material (TIM) which proves to be a great alternative to grease. It contains a solvent to assist in processing, which allows for wetting of the surface. However, after the solvent dries, it will be moistureless to the touch; therefore eliminating the mess associated with grease. Once the solvent is removed, Tpcm[™] 780SP begins to soften and flow at temperatures around 45°C, filling the microscopic irregularities of the components it contacts.

FEATURES AND BENEFITS

- Minimizes contact thermal resistance by filling the microscopic irregularities of the componenets it touches.
- Because Tpcm[™] 780SP softens but does not fully change states, it is designed to minimize migration (pump out) under thermal cycling from room temperature to chip device operating temperatures.
- Available in a 0.5 kg or 1.0 kg can for easy manual screen printing and large volume automatic applications.

APPLICATIONS

- High Frequency Microprocessors
- Notebook PCs
- Desktop PCs
- Computer Servers
- DC/DC Converterss
- Memory Modules
- Cache Chips
- IGBTs
- Automotive
- Optical

global solutions: local support ™

Americas: +1.888.246.9050 Europe: +49-(0)-8031-2460-0 Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com www.lairdtech.com/thermal



Tpcm[™] 780SP SeriesScreen Printable Phase Change Material Preliminary

SPECIFICATIONS

	VALUE	TEST METHOD
Color	Grey	Visual
Construction	Paste	
Viscosity at 25°C (Pa-s) (cPs)	35 50,000 - 100,000	Rheometer - Laird Technologies' custom method Brookfield, Spindle T-D, 10 rpm
Specific Gravity (g/cc)	2.48 (without solvent) 2.20 (with 3.5% solvent)	Helium Pycnometer
Softening Range (°C)	45 to 70	
Shelf Life (months)	6	
Thermal Conductivity (no solvent) (W/mK)	5.4	Hot Disk Thermal Contants Analyzer
Thermal Impedance (°C-in2/W, °C-cm2/W) @ 50 psi (345 kPa)	0.004, 0.025	ASTM E5470 (pressure modified)
Outgassing TML	~0.51%	ASTM E595
Outgassing CVCM	~0.20%	ASTM E595

^{*}Based on 2000 cycles. See data chart on reverse side

Storage: Store from 5° C to 35° C with a maximum humidity of 50% and with lid tightly closed. Do not store in a freezer or refrigerator at 5° C or below.

Application:

*Mix can thoroughly prior to use, best results using a jar roller at a 20 to 30 degree angle for 30 minutes or longer. A stencil or screen mesh of 61 TPI (threads per inch) or less is recommended for easiest application, however the phase change has been successfully applied using up to a 140 mesh screen (the higher the number = smaller screen opening).

global solutions: local support ™

Americas: +1.888.246.9050 Europe: +49.(0).8031.2460.0 Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com www.lairdtech.com/thermal

THR-DS-TPCM780SP 0911

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the finess, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential diamages of any kind. All Laird Technologies for any composition of the incidental or consequential diamages of any kind. All Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trade marks or registered trade marks or Laird Technologies for or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights. A16426-00 Rev B

^{*}Solvent evaporates within two hours at 60° C, or 8 hours at room temeperature. After solvent evaporation, the TpcmTM 780SP will be firm and dry to the touch.